



DMV540B

MINI OTOSCOPE REGULAR LIGHT

- High quality blue otoscope for pocket and doctor's bag
- Unobstructed vision with fibre optic illumination with 2.5 V XHL Xenon halogen lamp
- Robust and light weight plastic with metal inserts and 3x rotating magnifying glass
- Handle requires 2 batteries (AA) and it is equipped with grooves for a better grip
- Speculum input is rapid and stable
- Provided with bag and with 4 additional reusable specula

DIR/QM – Rev. 02_04/09/2024

For further information and/or technical data related to the product, please refer to the Oscar Boscarol Company.