



#### **DMV540N**

### **MINI OTOSCOPE WITH CONVENTIONAL LIGHT**

- High quality black otoscope for pocket and doctor's bag
- Unobstructed view, unit equipped with halogen Xenon bulb
- Robust and light weight plastic with metal inserts
- Equipped with 3x rotating magnifying glass
- The handle requires 2 batteries (AA) and it is equipped with grooves for a better grip
- Speculum input is rapid and stable
- Provided with bag and with 4 additional reusable specula

*DIR/QM – Rev. 01\_01/03/2024*

For further information and/or technical data related to the product, please refer to the Oscar Boscarol Company.